


3R**Anyty™****DEJiKEN**

WIFI DIGITAL MICROSCOPE

With WiFi connection, object can be seen directly on tablet or smart mobile phone, also you can take and stored pictures directly on tablet or phone.



3R-WM401 WIFI
same magnification
10~200 times



Smart Phone




PC (browser)

◀ Cable Connection

If the wireless transmission is restricted in one environment, you can chose cable connection.

450~600 times



3R-WM601 WIFI
450~600 times

Download Free APP IOS or Android

You can use the APP to observe or take photograph.



ios App



Android App

Wifi connection and remote control it can be used under the condition which radio data transmission is interfered. With WiFi you can take photographs or save picture on mobile phone or tablet. The working range is about 5 meters, It can be connected to 5 devices at the same time.



Recommendation tablet
If you do not have WiFi device, we recommend the tablet.

This computer is products of ASUS company. ASUS retains the right of upgrade tablet without notice.

3R-WM401 WIFISSET
3R-WM601 WIFISSET
3R-WM461 WIFISSET



Observe on tablet or smart mobile phone! Taking photo and saving pictures!

Special software to connect through WiFi

No cable required, wifi enabled snapshot via phone or tablet, here comes the new microscope! With WiFi connection you can observe and analyze object on mobile phone or tablet (IOS/Android). Of course, you can also take photograph and store directly in phone or tablet.



The special built-in software with measurement tool

After data correction you can measure the distance between two points or angles, and the picture with data can be saved directly.



Picture Comparison

● Different observation comparison (60 times)




● Scalp

● Fiber

● Plant

● Magnification comparison (e.g. dot)



● Chip

● 60times

● 150times

● 200times

● 600times

Packing list

■ 3R-WM401WIFI



- 200 times microscope body
- 60/200 times lens cover
- 80/150 times lens cover
- 100 times lens cover

■ 3R-WM601WIFI



- 600 times microscope body
- 500 times lens cover
- 600 times lens cover

■ 3R-WM461WIFI



- 200/600 times body
- Lens cover (5 kinds):
- 60/200 times • 500 times • 600 times
- 80/150 times • 100 times

■ Same accessories



- Stand
- Holder
- Mini USB Cable
- Scale
- AC/USB Adapter
- Instruction manual
- Software manual

Specification

Inner sense	1/4 inch CMOS sensor
Sense resolution	1300000 resolution
White balance	Automatic
Exposure	Automatic
Light	White LED*8
Signal transmission	IEEE802.11b/g/n
Hertz	2.400~2.4835GHz
Using Distance	5m
Magnification	Equal size of object (◎) 10-200times(3R-WM401WIFI) 450-600 times (3R-WM601WIFI)
Focal distance	8-300mm/about 1000mm (◎) (3R-WM401WIFI) 1-14mm (3R-WM601WIFI)
Battery	Rechargeable lithium battery
Power	DC5V1A
Charging time	About 3 hours
Working time	About 2 hours
Repeated charging	About 500 times
Size	Φ36*142mm
Weight	About 82 g
Work temperature	-10~50°C
Work humidity	15~85%

◎ It will be equal size of object when focal distance is over 300mm.

Recommend version

Android		IOS	
OS	Above android 4.1	OS	IOS6/7 Above
CPU	Above dual core	IPhone	4S version and above
Memory	Above 1 GB	IPad	IPad2 above
Resolution	Above 854*480	IPad mini	Above 1 generation
Wireless LAN	IEEE802.11b/g/n	IPod touch	Above 5 generation
Windows		OSX	
OS	Windows8.1/8/7/vista	OS	Mac OSX 10.6 above
CPU	Core 2 Duo 2.0GHz above	CPU	Core 2 Duo 2.0GHz above
Memory	Above 2GB	Memory	Above 2GB
Storage space requirements:		Storage space requirements:	
10 GB above		10 GB above	
Resolution:		Resolution:	
XGA(1024*768) above		XGA(1024*768) above	
Graphic WDDM 1.0 above		Graphic Intel HD Graphics above	
Wireless LAN:		Wireless LAN:	
IEEE802.11b/g/n		IEEE802.11b/g/n	

* please notice that the recommended version might not work because of the nuances of each version.



3R system limited company

3R SYSTEMS CORP

Headquarters 812-0893 5-8-11. Naka Hakata, Fukuoka, Japan, ZPI:812-0893

● support service : Info@3rrr.co.jp <http://www.3rrr.co.jp>

TEL 092-441-4056 FAX 092-441-4077

Selling shop :